



Catalog No. TH4365RC

Description: 400A 3P HD N3R 600V FUSIBLE CSA

UPC No 783164422665

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Suitable for use as service equipment when installed in accordance with the Canadian Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	400 A
Poles	3
Wires	4
Fusing	Fusible
Enclosure	NEMA 3R (Outdoor)
Options	CSA SE Rated
Wire Range (Cu/Al)	(1) 2-600 or (2) 1/0-250
240 Vac, NEC Std, 3-ph	50
240 Vac, Time Delay, 3-ph	125
480 Vac, NEC Std, 3-ph	100
480 Vac, Time Delay, 3-ph	250
600 Vac, NEC Std, 3-ph	125
600 Vac, Time Delay, 3-ph	350
250 Vdc	50
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	No

Dimensions

Height	49.5
Depth	8.5
Width	23
Weight	130

Publications

Title	Publication No.	Publication Type
Safety Switch HD Outline Drawing 600A , NEMA 3R Enclosure	10103091SH140	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.