



**Catalog No. THQB22035**

**Description: THQB C E**

**UPC No 783164118469**

**Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line**

**Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

**Descriptors**

|             |                                   |
|-------------|-----------------------------------|
| Category    | Q-Line Miniature Circuit Breakers |
| GO Schedule | EB                                |

**Specifications**

|                                 |                               |
|---------------------------------|-------------------------------|
| Trip Style                      | Non-Interchangeable           |
| Frame Type                      | Q-Line                        |
| Amperage                        | 35 A                          |
| System Voltage                  | 120 Vac, 120/240 Vac, 240 Vac |
| Poles                           | 2                             |
| Trip Function                   | LI                            |
| Continuous Current Rated        | Standard                      |
| 120 Vac Interrupting Rating     | 22 KAIC                       |
| 120/240 Vac Interrupting Rating | 22 KAIC                       |
| 240 Vac Interrupting Rating     | 22 KAIC                       |
| Suitable for Reverse Feed       | Yes                           |
| Product Line                    | TEY / Q-Line (Bolt-On)        |
| Long Time                       | Fixed                         |
| Instantaneous                   | Fixed                         |
| Protective Relays               | No                            |
| Current Metering                | No                            |
| Special Markings                | HACR                          |
| GSA Compliance                  | No                            |

**Classifications**

|           |        |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|

## Publications

| Title  | Publication No. | Publication Type                 |
|--|-----------------|----------------------------------|
| <a href="#">Q-Line Bolt-On MCCB, 100A Frame 1-, 2-, or 3- Pole, Drawing</a><br>1-Page fully dimensioned outline drawing in .pdf format | 455C873-SH1     | Drawings-Outline and Dimensional |

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.