



**Catalog No. THHQC2160LL**

**Description: 2 POLE 120/240V 22KA 60A W/NO LUGS**

**UPC No 783164109382**

**Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QC breakers are lug-lug versions of the Q Line and are available for 35mm DIN rail mounting. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions and can be ordered with auxiliary contact and shunt trip accessories.

**Descriptors**

Category	Q-Line Miniature Circuit Breakers
GO Schedule	EB

**Specifications**

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	60 A
System Voltage	120 Vac, 120/240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
Suitable for Reverse Feed	Yes
Product Line	Q-Line (Lug-Lug)
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

**Classifications**

UL File #	E11592
-----------	--------

## Publications

Title	Publication No.	Publication Type
Q-Line Lug-Lug, Din Rail Mountable MCCB, 100A Frame 2- Pole , Drawing 1-Page fully dimensioned outline drawing in .pdf format	208C3604-SH2	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.