



Catalog No. THKMA826800

Description: MCCB 800A 2P 600V W/LOAD LUG KIT

UPC No 783164047394

Products > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The K1200 product line consists of Thermal Magnetic Circuit Breakers, Magnetic Circuit Breakers, and Molded-Case Switches rated up to 1200 Amps and 600 Volts AC. These breakers feature interchangeable trips on all frames. K1200 breakers are available in two frames, 800 ampere frame (300 to 800 amperes) and 1200 ampere frame (600 to 1200 amperes). Trip units are not interchangeable between frames. Complete circuit breaker price includes frame, trip, and Cu/Al line and load lugs. Units will be shipped unassembled unless specified "must be factory assembled". The WL catalog number suffix indicates that the devices come with Cu/Al line and load lugs. Magnetic Circuit Breakers must be ordered as components, including a frame, trip, and one line and one load lug per pole.

Descriptors

Category	Thermal Magnetic
GO Schedule	EL

Specifications

Frame Type	K1200
Amperage	800 A
Poles	2
Trip Function	LI
GSA Compliance	No