



## Catalog No. THN2261RDC

Description: 30A 2P HD N3R 600VDC NONFUSE SW

UPC No 783164082258

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed specifically for 600Vdc motor applications.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Voltage	600 DC
Amperage	30 A
Poles	2
Wires	2
Fusing	No Fuse
Enclosure	NEMA 3R (Outdoor)
Options	None
Wire Range (Cu/Al)	12-2
125 Vdc	3.0 hp
250 Vdc	5.0 hp
600 Vdc	15.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	13.1 in
Depth	4.0 in
Width	8.2 in
Weight	11.0 lb

## Publications

Title	Publication No.	Publication Type
<a href="#">60A - Safety Switches</a> 1 page outline drawing in .pdf format.	10103091-SH101	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.