



Catalog No. THN3361JW

Description: 30A 3P HD N5/12 600V NONFUSE WIN

UPC No 783164065145

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	30 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 5, 12 Drip/Dust-tight
Options	Viewing Window
Wire Range (Cu/Al)	12-2
240 Vac, NEC Std, 1-ph	3.0 hp
240 Vac, NEC Std, 3-ph	10.0 hp
480 Vac, NEC Std, 1-ph	7.5 hp
480 Vac, NEC Std, 3-ph	20.0 hp
600 Vac, NEC Std, 1-ph	10.0 hp
600 Vac, NEC Std, 3-ph	30.0 hp
250 Vdc	5.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	13.3 in
Depth	5.4 in
Width	9.4 in
Weight	16.0 lb

Publications

Title	Publication No.	Publication Type
60A (incl. -R suffix) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH110	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.