



## Catalog No. THN3362JW

Description: 60A 3P HD N5/12 600V NONFUSE WIN

UPC No 783164065152

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Voltage	600 AC
Amperage	60 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 5, 12 Drip/Dust-tight
Options	Viewing Window
Wire Range (Cu/Al)	12-2
240 Vac, NEC Std, 1-ph	10.0 hp
240 Vac, NEC Std, 3-ph	20.0 hp
480 Vac, NEC Std, 1-ph	20.0 hp
480 Vac, NEC Std, 3-ph	50.0 hp
600 Vac, NEC Std, 1-ph	25.0 hp
600 Vac, NEC Std, 3-ph	60.0 hp
250 Vdc	10.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	No
UL Listed	Yes

### Dimensions

Height	19.3 in
Depth	5.7 in
Width	9.4 in
Weight	21.0 lb

## Publications

Title	Publication No.	Publication Type
60A (incl. -R suffix) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH110	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.