



Catalog No. THN3362RF

Description: 60A 3P HD N3R 600V NONFUSE

UPC No 783164338362

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for outdoor disconnect applications such as irrigation systems and farm equipment.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.
- NEMA type 3R oversized enclosure with side-swing cover.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	60 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 3R (Outdoor)
Options	Farm Switch
Wire Range (Cu/Al)	12-2
250 Vdc	10
GSA Compliance	No

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	22.4
Depth	4.8
Width	13.3
Weight	22

Publications

Title	Publication No.	Publication Type
60A (-RF suffix) - Safety Switches	10103091-SH134	Drawings-Outline and Dimensional
1 page outline drawing in .pdf format.		

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.