



**Catalog No. THN3364JA64D**

**Description: 200A 3P HD N5/12 600V NONFUSE**

**UPC No 783164019933**

**Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty**

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

**Descriptors**

Category	Heavy Duty
GO Schedule	S1

**Specifications**

Amperage	200 A
Poles	3
Fusing	No Fuse
GSA Compliance	No