



## Catalog No. THN3364SS-BA

Description: 200A 3P HD N4X SS 600V NONFUSE USA

UPC No 783164450576

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Voltage	600 AC
Amperage	200 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 4/4X Water/Dust-tight
Options	None
Wire Range (Cu/Al)	2-250
240 Vac, NEC Std, 3-ph	60.0 hp
480 Vac, NEC Std, 1-ph	50.0 hp
480 Vac, NEC Std, 3-ph	125.0 hp
600 Vac, NEC Std, 1-ph	50.0 hp
600 Vac, NEC Std, 3-ph	150.0 hp
250 Vdc	40.0 hp
GSA Compliance	No

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	35.1 in
Depth	5.2 in
Width	14.5 in
Weight	50.0 lb

## Publications

Title	Publication No.	Publication Type
200A (incl. 316 Stainless) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH113	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.