



## Catalog No. THN3365SSA66D

Description: 400A 3P HD N4X SS 600V NONFUSE

UPC No 783164020052

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.
- NEMA type 4X enclosure grade 316 stainless steel.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Amperage	400 A
Poles	3
Fusing	No Fuse
Enclosure	NEMA 4/4X (316 Stainless)
Options	None
240 Vac, NEC Std, 3-ph	125
480 Vac, NEC Std, 3-ph	250
600 Vac, NEC Std, 3-ph	350
250 Vdc	50
GSA Compliance	No

### Classifications

CSA Certified	No
UL Listed	Yes

### Dimensions

Height	59.5
Depth	8.4