



Catalog No. THN6664

Description: 200A 6P SW N1/3R/5/12 600V NONFUSE

UPC No 783164121186

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	200 A
Poles	6
Wires	6
Fusing	No Fuse
Enclosure	NEMA 1, 3R, 5/12
Options	None
Wire Range (Cu/Al)	2-250
240 Vac, NEC Std, 1-ph	15.0 hp
240 Vac, NEC Std, 3-ph	50.0 hp
480 Vac, NEC Std, 3-ph	125.0 hp
600 Vac, NEC Std, 1-ph	50.0 hp
600 Vac, NEC Std, 3-ph	150.0 hp
250 Vdc	40.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	35.1 in
Depth	5.7 in
Width	26.0 in
Weight	47.0 lb

Publications

Title	Publication No.	Publication Type
200A (6 Pole) - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH127	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.