



**Catalog No. THQD22175**

**Description: THQD 2 POLE 240V 22K IC 175 AMP**

**UPC No 783164087857**

**Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line**

**Miniature Circuit Breakers**

The TQD Line of devices include thermal magnetic molded case circuit breakers and molded case switches. The devices are complete with Cu/Al line and load lugs.

**Descriptors**

Category	Q-Line Miniature Circuit Breakers
GO Schedule	EF

**Specifications**

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	175 A
System Voltage	120 Vac, 120/240 Vac, 240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
240 Vac Interrupting Rating	22 KAIC
Lugs	TCAL25
Suitable for Reverse Feed	Yes
Wire Range (Cu/Al)	(2) 1-300
Product Line	Thermal Magnetic
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

**Classifications**

UL File #	E11592
-----------	--------

## Publications

Title	Publication No.	Publication Type
<a href="#">225A GE METER STACKS</a> 225A Sockets Outline Drawing	DEE-872	Drawings-Outline and Dimensional
<a href="#">TQD / THQD MCCB, 2- and 3- Pole 100-225 Ampere, Drawing</a> 1 page, Non-dimensioned full scale layout drawing in .dxf format	TQD225 2-3P-DXF	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.