



**Catalog No. THQD22225WL**

**Description: 2 POLE 240V 22K IC 225 AMP W/LUGS**

**UPC No 783164087901**

**Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line**

**Miniature Circuit Breakers**

The TQD Line of devices include thermal magnetic molded case circuit breakers and molded case switches. The devices are complete with Cu/Al line and load lugs.

**Descriptors**

Category	Q-Line Miniature Circuit Breakers
GO Schedule	EF

**Specifications**

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	225 A
System Voltage	120 Vac, 120/240 Vac, 240 Vac
Poles	2
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
240 Vac Interrupting Rating	22 KAIC
Lugs	TCAL25
Suitable for Reverse Feed	Yes
Product Line	Thermal Magnetic
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

**Classifications**

UL File #	E11592
-----------	--------

## Publications

Title	Publication No.	Publication Type
<a href="#">TQD / THQD MCCB, 2- Pole 100-225 Ampere, Drawing</a> 1 page, Fully Dimensioned Layout Drawing in .dxf format	455C765-SH3-DXF	Drawings-Outline and Dimensional
<a href="#">TQD / THQD MCCB, 2- and 3- Pole 100-225 Ampere, Drawing</a> 1 page, Non-dimensioned full scale layout drawing in .dxf format	TQD225 2-3P-DXF	Drawings-Outline and Dimensional
<a href="#">TQD / THQD MCCB, 2- Pole 100-225 Ampere, Drawing</a> 1 page, Fully Dimensioned Layout Drawing in .pdf format	455C765-SH3	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.