



## Catalog No. THQP145

**Description:** THQP 1 POLE 120/240V 10K IC 45 AMP

**UPC No** 783164134469

**Products > Circuit Breakers > Residential Circuit Breakers > Feeder Plug-in Circuit Breakers**

THQP breakers are a smaller, smarter solution for today's cost- and quality-conscious contractors and homeowners. Half the width of standard breakers, they allow use of smaller load centers and for maximum savings of space and money. GE is the only manufacturer that gives you this cost advantage without sacrificing flexibility. THQP breakers are one-half the width of standard GE breakers but identical in design. They are available from 15 to 50 amps and in single and two pole construction.

### Descriptors

Category	Feeder Plug-in Circuit Breakers
GO Schedule	R5

### Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	45 A
System Voltage	120 Vac, 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Wire Range (Cu/Al)	8-4 kcmil / 8-4 kcmil
Product Line	Q-Line (Plug-In)
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

### Classifications

UL File #	E11592
-----------	--------

## Publications

Title	Publication No.	Publication Type
<a href="#">Q-Line Plug-In MCCB, 100A Frame 1-, 2- Pole, Drawing</a> 1-Page fully dimensioned outline drawing in .pdf format	139C5337-SH1	Drawings-Outline and Dimensional
<a href="#">Ground Fault Circuit Interrupter with Self-Test Feature (GFCI)</a> Rev A. 2 Pages. Installation, troubleshooting, and testing guide for type THQ/THHQ 15A-30A, 2 Pole circuit breakers.	GEH-4339	Installation and Instruction

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.