



Catalog No. TJ400R

Description: ASM RAINIGHT ENCLOSURES

UPC No 783164013412

Products > Circuit Breakers > Circuit Breaker Enclosures

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Frame notes and/or restrictions: Enclosure can also be used with TJD.

Enclosure notes and/or limitation: Suitable for parallel 250 kcmil cable maximum (use 600 amp enclosure if larger cable is required).

Enclosure does not include removable closing cap.

Order raintight hub separately (requires field cut).

ACCESSORIES:

Neutral Kit (non-GF applications): TNIA400

Raintight Hubs: TC200, TC250, TC300, TCCP

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B3

Specifications

Enclosure Type	NEMA Type 3R
Mounting	Surface
Frame Type	J600
Amperage	400 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5498SH4
GSA Compliance	No

Dimensions

Height	27.3 in
Depth	8.0 in
Width	15.7 in
Weight	37.6 lb

Publications

Title	Publication No.	Publication Type
NEMA Type 3R enclosure, 400 amp max. Product Number TJ400R. 1 page outline drawing in .pdf format.	139C5498-SH4	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.