



**Catalog No. TJ600J**

**Description: TYPE 12 ENCL 600A SURFACEW/O KO**

**UPC No 783164013474**

**Products > Circuit Breakers > Circuit Breaker Enclosures**

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Enclosure notes and/or limitation: Enclosure does not include knockouts (NEMA Type 12).

ACCESSORIES:

Neutral Kit (non-GF applications):TNIA600

**Descriptors**

Category	Circuit Breaker Enclosures
GO Schedule	B2

**Specifications**

Enclosure Type	NEMA TYPE 12/12K
Mounting	Surface
Frame Type	J600
Amperage	600 A
UL/CUL Listing	CSA, UL
Material	Steel
Drawings-Outline and Dimensional	139C5682SH5
GSA Compliance	No

**Dimensions**

Height	48.4 in
Depth	8.4 in
Width	17.7 in
Weight	85.1 lb

## Publications

Title	Publication No.	Publication Type
NEMA Type 12 and 12K enclosure, 600 amp max. Product Number TJ600J. 1 page outline drawing in .pdf format.	139C5682-SH5	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.