



Catalog No. TJC36400E

Description: 3 POLE 600V 400 AMP MAG BREAK C.B.

UPC No 783164135589

Products > Circuit Breakers > Molded Case Circuit Breakers > Mag-Break® Motor Circuit Protector

MagBreak Motor Circuit Protectors have an adjustable instantaneous trip system and are UL recognized components.

Descriptors

Category	Mag-Break® Motor Circuit Protector
GO Schedule	EL

Specifications

Product Line	Thermal Magnetic
Trip Style	Non-Interchangeable
Frame Type	J600
Amperage	400 A
Poles	3
System Voltage	120 Vac, 120/240 Vac, 240 Vac, 277 Vac, 480 Vac, 600 Vac
120 Vac Interrupting Rating	42 KAIC
120/240 Vac Interrupting Rating	42 KAIC
240 Vac Interrupting Rating	42 KAIC
277 Vac Interrupting Rating	30 KAIC
480 Vac Interrupting Rating	30 KAIC
600 Vac Interrupting Rating	22 KAIC
Trip Function	Mag Only
Continuous Current Rated	Standard
Suitable for Reverse Feed	No
Lugs	TCAL47
Long Time	No
Instantaneous	Adjustable
Current Metering	No
Protective Relays	No
GSA Compliance	No

Classifications

UL File #	E11592
-----------	--------

Publications

Title	Publication No.	Publication Type
Mag-Break Motor Circuit Protector, TJC 600 Frame 1-Page fully dimensioned outline drawing in .pdf format	456C395-DB	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.