



Catalog No. TJD422250WL

Description: TJD 2 POLE 240V 250 AMP - WL

UPC No 783164049152

Products > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

The TJD Line of devices include thermal magnetic molded case circuit breakers and molded case switches. The devices are complete with Cu/Al line and load lugs.

Descriptors

Category	Thermal Magnetic
GO Schedule	E3

Specifications

Product Line	Thermal Magnetic
Trip Style	Non-Interchangeable
Amperage	250 A
Poles	2
System Voltage	120 Vac, 120/240 Vac, 125 Vdc, 240 Vac, 250 Vdc
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
125 Vdc Interrupting Rating	10 KAIC
240 Vac Interrupting Rating	22 KAIC
250 Vdc Interrupting Rating	10 KAIC
Trip Function	LI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TCAL43, TCAL47
Long Time	Fixed
Instantaneous	Fixed
Current Metering	No
Protective Relays	No
GSA Compliance	No

Classifications

UL File #	E11592
-----------	--------

Publications

Title	Publication No.	Publication Type
Q-Line Lug-Lug MCCB, 400A Frame 2- or 3-Pole, Drawing 1-Page, Fully dimensioned outline drawing in .pdf format	139C3602-SH1	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.