



Catalog No. TL42422R

Description: MLO 225A 42CRT 3P4W 208Y/120V 3R

UPC No 783164062410

Products > Load Centers > Commercial/High-rise Residential > Three Phase

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Three Phase
GO Schedule	R7

Specifications

Input/Output Voltage	208Y/120V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	225 A
Device Type	Main Lugs
Enclosure	Outdoor Type 3R Enclosure
UL/CUL Listing	UL
Phase	3 Phase
Socket Type	0
1" Space	42
1/2" Space	42
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outdoor Load Center 1 page outline drawing in pdf format.	10103091-SH6	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.