



Catalog No. TLM2012CCURP

Description: 125A 20 CIRC INDOOR RISER PANEL

UPC No 783164287899

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Single Phase - USA
GO Schedule	RA

Specifications

Input/Output Voltage	120/240V ac
Type	Riser Panel
Interrupting Capacity Rating	22
Amperage	125 A
Device Type	Convertible
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	20
1/2" Space	24
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
PowerMark Gold Commercial Accessories 2 page data sheet includes features and photos for PowerMark Gold Riser Panel, auxiliary gutter and three pole subfeed lugs, catalog number selection guide table, wiring diagrams, listing of accessories and options. Indoor Load Center	DET-223A	Application and Technical
1 page outline drawing in pdf format.	10103091-SH66	Drawings-Outline and Dimensional
PowerMark Gold Commercial Accessories 2 page data sheet includes features and photos for PowerMark Gold Riser Panel, auxiliary gutter and three pole subfeed lugs, catalog number selection guide table, wiring diagrams, listing of accessories and options.	DET-223	Application and Technical

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.