



Catalog No. TLM3220CCUW

Description: 150/200A CONV LC 32-40 CRT N1 WHIT

UPC No 783164395907

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Single Phase - USA
GO Schedule	RD

Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	200 A
Device Type	Convertible
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	32
1/2" Space	40, 42, 4, 24, 16, 20, 32
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
White front load centers US - DEE590A	DEE-590A	Brochures

2 pages. PowerMark Gold 125-225 Amp Load Centers with White Fronts. Same great GE PowerMark Gold load centers now available with a white front from the factory!

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.