



Catalog No. TLM812SCUD1K

Description: FLD CNVRTB 125A 8CT 120/240V KIT

UPC No 783164302875

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Single Phase - USA
GO Schedule	RD

Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	125 A
Device Type	Convertible
Enclosure	Indoor Type 1 Enclosure, Surface Mount
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	8
1/2" Space	42, 4, 24, 16
Feed	Either
Door	Yes
GSA Compliance	No