



## Catalog No. TM10RMC

Description: MtrMain Ring 100A Surf 0/0 Ckt OH/UG N3R

UPC No 783164305036

Products > Load Centers > Residential Load Centers > Meter Socket

- 100 Amp Meter Main with 100 amp main breaker factory installed
- 10kAIC RMS symmetrical, except where noted
- Georgia Power compliant
- UL Listed (Panelboards No. 67)
- Surface mount, NEMA Type 3R enclosure (outdoor/rainproof)
- Overhead and underground feed
- 75°C Conductor Rating
- Suitable only for use as service entrance equipment when Installed in accordance with the National Electrical Code

### Descriptors

Category	Meter Socket
GO Schedule	RB

### Specifications

Input/Output Voltage	120/240V ac
Type	Factory Included Ground Bar
Interrupting Capacity Rating	10
Amperage	100 A
Device Type	Meter Socket
Enclosure	Surface Type 3R, Outdoor Type 3R Enclosure
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	1
1" Space	0
1/2" Space	4, 0
Feed	Either
Door	Yes
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">Outdoor Load Center</a> 1 page outline drawing in pdf format.	10103091-SH30	Drawings-Outline and Dimensional
<a href="#">Outline Drawing for Part # TM10RMC</a> Meter Main - Ring - 100A MCB TQD - 0/0 Circuits - N3R Encl - Surface Front - OH/UG Incoming Feed - UL Listed	TM10RMC	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.