



**Catalog No. TM2420R42B**

**Description: 24 42 CKT 200A BOTTOM FED N3R LC**

**UPC No 783164396539**

**Products > Load Centers > Residential Load Centers > Single Phase - USA**

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit [www.geelectrical.com](http://www.geelectrical.com)

**Descriptors**

Category	Single Phase - USA
GO Schedule	RD

**Specifications**

Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Amperage	200 A
Enclosure	Outdoor Type 3R Enclosure
UL/CUL Listing	UL
Phase	1 Phase
1" Space	24
1/2" Space	36
Feed	Either
Door	No
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">Outdoor Load Center</a> 1 page outline drawing in pdf format.	10103091-SH10	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.