



Catalog No. TM2440RMS

Description: MSLC MCB Dual Ring 400A 24/40 SF UG EUSC

UPC No 783164229752

Products > Load Centers > Residential Load Centers > Meter Socket

400A Meter Socket Load Center 24 Circuit Ring Style

Descriptors

Category	Meter Socket
GO Schedule	RB

Specifications

Input/Output Voltage	120/240V ac
Type	Meter Socket
Interrupting Capacity Rating	22
Amperage	400 A
Device Type	Meter Socket
Enclosure	Surface Type 3R, Outdoor Type 3R Enclosure
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	1
1" Space	24
1/2" Space	6, 12, 16, 20, 24, 32
Feed	Bottom
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outdoor Load Center 1 page outline drawing in pdf format.	10103091-SH36	Drawings-Outline and Dimensional
Outline Drawing for Part # TM2440RMS Main Breaker Dual - Ring - TQD - 400A - 10K -24/40 Circuits - N3R Encl - SBS - Surface/Semiflush Front - UG Incoming Feed - EUSERC	TM2440RMS	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.