



**Catalog No. TM3215RCU**

**Description: 150A 32CT 1P3W 120/240V 22K IC 3R**

**UPC No 783164113112**

**Products > Load Centers > Residential Load Centers > Single Phase - USA**

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit [www.geelectrical.com](http://www.geelectrical.com)

**Descriptors**

Category	Single Phase - USA
GO Schedule	RD

**Specifications**

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	22
Amperage	150 A
Device Type	Main Breaker
Enclosure	Outdoor Type 3R Enclosure
UL/CUL Listing	UL
Phase	1 Phase
1" Space	32
1/2" Space	0
Feed	Top
Door	No
GSA Compliance	Yes

## Publications

Title	Publication No.	Publication Type
<a href="#">Outdoor Load Center</a> 1 page outline drawing in pdf format.	10103091-SH11	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.