



**Catalog No. TMH2440RMS**

**Description: MSLC MCBDual Ring 400A 24/40 SF UG EUSC**

**UPC No 783164231922**

**Products > Load Centers > Residential Load Centers > Meter Socket**

400A Meter Socket Load Center 24 Circuit Ring Style

**Descriptors**

Category	Meter Socket
GO Schedule	RB

**Specifications**

Input/Output Voltage	120/240V ac
Type	Meter Socket
Interrupting Capacity Rating	22
Amperage	400 A
Device Type	Meter Socket
Enclosure	Surface Type 3R, Outdoor Type 3R Enclosure
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	1
1" Space	24
1/2" Space	6, 12, 16, 20, 24, 32
Feed	Bottom
Door	Yes
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">Outdoor Load Center</a> 1 page outline drawing in pdf format.	10103091-SH36	Drawings-Outline and Dimensional
<a href="#">Outline Drawing for Part # TMH2440RMS</a> Main Breaker Dual THQD - Ring - 400A - 22K - N3R Encl 24/40 Circuits - Semiflush Front - UG Incoming Feed - EUSERC	TMH2440RMS	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.