



Catalog No. TMPR312140TR

Description: MTR STK,1-400A RGLESS SKT,1200A,3PH,7T

UPC No 783164194302

Products > Metering > Modular Metering > Meter Mod III > GE Meter Stack Modules Single- and Three- Phase

Descriptors

Category	GE Meter Stack Modules Single- and Three- Phase
GO Schedule	QB

Specifications

Phase	Three-Phase, Four-Wire
Socket Amperage	400 A
Voltage	120/240 V ac, 208Y/120 V ac, 240/120 V ac
No of Sockets	1
Rating	400
Lever Bypass	Yes
Pull Box	No
GSA Compliance	No

Dimensions

Width	18.0 in
Height	52.6 in
Depth	8.7 in

Publications

Title	Publication No.	Publication Type
METER MODULE - 3PH 1200A HORIZONTAL BUSSING, (1)400A RINGLESS SOCKETS - LEVER BYPASS - N3R ENCL 1 page outline drawing in .pdf format.	TMPR312140TR	Drawings-Outline and Dimensional
TMPR312140TR BIM File	TMPR312140TR -BIM	BIM Files
METER MODULE, 1200A BUS, 3PH, (1) 400A SOCKET, RINGLESS, 7 TERMINAL/JAW, N3R, NO BREAKER INCLUDED, CAN'T SERVE (1) 400A LOAD. USE TO FEED (2) BREAKERS UP TO 400A SUMMED TOGETHER		

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.