



Catalog No. TSL412CSCU

Description: MSLC MLO Rng 125A22K 4/8 S UGOH Xcel Col

UPC No 783164197969

Products > Load Centers > Residential Load Centers > Meter Socket

125A Meter Socket Load Center 4 Circuit Ring Type OH/UG Surface Mount

Descriptors

Category	Meter Socket
GO Schedule	RB

Specifications

Input/Output Voltage	120/240V ac
Type	Breaker
Interrupting Capacity Rating	10
Amperage	125 A
Device Type	Meter Socket
Enclosure	Surface Type 3R
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	1
1" Space	4
1/2" Space	24, 20, 6, 12, 16
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outdoor Load Center 1 page outline drawing in pdf format.	10103091-SH85	Drawings-Outline and Dimensional
Outline Drawing for Part # TSL412CSCU Main Lug Only - Ringless - 125A 22K - 4/8 Circuits - N3R Encl - Surface Front - OH/UG Incoming Feed - Horn Bypass - EUSERC	TSL412CSCU	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.