



Catalog No. TSLR412CSCU

Description: MSLC MLO Rgls 125A 20/40 S UGOH HB Xcel

UPC No 783164198096

Products > Load Centers > Residential Load Centers > Meter Socket

125A Meter Socket Load Center 4 Circuit Ringless Surface Mount

Descriptors

Category	Meter Socket
GO Schedule	RB

Specifications

Input/Output Voltage	120/240V ac
Type	Lugs(field installed Main)
Interrupting Capacity Rating	22
Amperage	125 A
Device Type	Meter Socket
Enclosure	Semi-Flush Type 3R
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	2
1" Space	4
1/2" Space	4
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outdoor Load Center 1 page outline drawing in pdf format.	10103091-SH70	Drawings-Outline and Dimensional
Outline Drawing for Part # TSLR412CSCU Main Lug Only - Ringless - 125A 22K- 4/8 Circuits - N3R Encl - Surface Front - UG/OH Incoming Feed - Horn Bypass - XCEL	TSLR412CSCU	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.