



**Catalog No. TSM1610CFCU**

**Description: MSLC MB Ring 100A10K 16/32 F UG/OH EUSC**

**UPC No 783164198294**

**Products > Load Centers > Residential Load Centers > Meter Socket**

100A Meter Socket Load Center 16 Circuit Ring Type OH/UG Semi Flush

**Descriptors**

Category	Meter Socket
GO Schedule	RB

**Specifications**

Input/Output Voltage	120/240V ac
Type	Breaker
Interrupting Capacity Rating	22
Amperage	100 A
Device Type	Meter Socket
Enclosure	Semi-Flush Type 3R
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	1
1" Space	16
1/2" Space	16, 20, 6, 12
Feed	Either
Door	Yes
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">Outdoor Load Center</a> 1 page outline drawing in pdf format.	10103091-SH72	Drawings-Outline and Dimensional
<a href="#">Outline Drawing for Part # TSM1610CFCU</a> Main Breaker THHQL- Ring - 100A 22K - 16/32 Circuits - N3R Encl Semiflush Front - UG/OH Incoming Feed - EUSERC Listed	TSM1610CFCU	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.