



Catalog No. TSM1612CSCU

Description: MSLC MB Ring 125A10K 16/32 S UG/OH EUSC

UPC No 783164198232

Products > Load Centers > Residential Load Centers > Meter Socket

125A Meter Socket Load Center 16 Circuit Ring Type OH/UG Surface Mount

Descriptors

Category	Meter Socket
GO Schedule	RB

Specifications

Input/Output Voltage	120/240V ac
Type	Breaker
Interrupting Capacity Rating	22
Amperage	125 A
Device Type	Meter Socket
Enclosure	Surface Type 3R
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	1
1" Space	16
1/2" Space	24, 20, 6, 12, 16
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outdoor Load Center 1 page outline drawing in pdf format.	10103091-SH71	Drawings-Outline and Dimensional
Outline Drawing for Part # TSM1612CSCU Main Breaker THHQL - Ring - 125A 22K- 16/32 Circuits - N3R Encl - Surface Front - UG/OH Incoming Feed - EUSERC Listed	TSM1612CSCU	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.