



Catalog No. TSM415CSCU

Description: MSLC MB Rng 150A22K 4/8 ckt Surf UG/OH

UPC No 783164308921

Products > Load Centers > Residential Load Centers > Meter Socket

150A Main Breaker Meter Socket Load Center 4/8 Circuit Surface Mount w Feed Thru Lugs

Descriptors

Category	Meter Socket
GO Schedule	RB

Specifications

Input/Output Voltage	120/240V ac
Type	Factory Included Ground Bar
Interrupting Capacity Rating	10
Amperage	150 A
Device Type	Meter Socket
Enclosure	Surface Type 3R
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	1
1" Space	4
1/2" Space	4
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outdoor Load Center 1 page outline drawing in pdf format.	10103091-SH86	Drawings-Outline and Dimensional
Outline Drawing for Part # TSM415CSCU Main Breaker THQMV- Ring - 150A 22K - 4/8 Circuits - N3R Encl - Surface Front - UG/OH Incoming Feed - UL Listed	TSM415CSCU	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.