



**Catalog No. TSMR1212CSCU**

**Description: MSLC MB Rgls 200A 20/40 S UGOH HB Xcel**

**UPC No 783164198850**

**Products > Load Centers > Residential Load Centers > Meter Socket**

125A Meter Socket Load Center 12 Circuit Ringless Surface Mount

**Descriptors**

Category	Meter Socket
GO Schedule	RB

**Specifications**

Input/Output Voltage	120/240V ac
Type	Breaker
Interrupting Capacity Rating	22
Amperage	125 A
Device Type	Meter Socket
Enclosure	Surface Type 3R
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	2
1" Space	12
1/2" Space	24, 6, 12, 16, 20
Feed	Either
Door	Yes
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">Outline Drawing for Part # TSMR1212CSCU</a>	TSMR1212CSCU	Drawings-Outline and Dimensional
Main Breaker THHQL - Ringless - 125A 22K - 12/24 circuits - N3R Encl Surface Front - UG/OH Incoming Feed - Horn Byp - XCEL Listed <a href="#">Outdoor Load Center</a>	10103091-SH69	Drawings-Outline and Dimensional
1 page outline drawing in pdf format.		

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.