



Catalog No. TSMR2015CSCU

Description: MSLC MB RglS 150A 20/40 S UGOH HB Xcel

UPC No 783164199024

Products > Load Centers > Residential Load Centers > Meter Socket

150A Meter Socket Load Center 20 Circuit Ringless Surface Mount

Descriptors

| | |
|-------------|--------------|
| Category | Meter Socket |
| GO Schedule | RB |

Specifications

| | |
|------------------------------|-------------------|
| Input/Output Voltage | 120/240V ac |
| Type | Breaker |
| Interrupting Capacity Rating | 22 |
| Amperage | 150 A |
| Device Type | Meter Socket |
| Enclosure | Surface Type 3R |
| UL/CUL Listing | UL |
| Phase | 1 Phase |
| Socket Type | 2 |
| 1" Space | 20 |
| 1/2" Space | 24, 6, 12, 16, 20 |
| Feed | Either |
| Door | Yes |
| GSA Compliance | No |

Publications

| Title | Publication No. | Publication Type |
|---|-----------------|----------------------------------|
| Outline Drawing for Part # TSMR2015CSCU | TSMR2015CSCU | Drawings-Outline and Dimensional |
| Main Breaker THQMV - Ringless - 150A 22K- 20/40 Circuits - N3R Encl - Surface Front - UG/OH Incoming Feed-Horn Byp - XCEL Listed Outdoor Load Center | 10103091-SH69 | Drawings-Outline and Dimensional |
| 1 page outline drawing in pdf format. | | |

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.