



Catalog No. TSMR2020CSCUFMG

Description: MSLC MB RgIs 200A 20/40 S UGOH MEG

UPC No 783164415179

Products > Load Centers > Residential Load Centers > Meter Socket

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Meter Socket
GO Schedule	RB

Specifications

Input/Output Voltage	120/240V ac
Type	Florida Metering Group
Interrupting Capacity Rating	22
Amperage	200 A
Device Type	Meter Socket
Enclosure	Outdoor Type 3R Enclosure
UL/CUL Listing	UL FMG
Socket Type	1
1" Space	20
1/2" Space	40
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outline Drawing for Part # TSMR2020CSCUFMG Main Breaker THQMV - Ringless - 200A 22K - 20/40 Circuits - N3R Encl - Top/Bottom - Surface Front - UG/OH Incoming Feed - MEG Listed	TSMR2020CSCUFMG	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.