



Catalog No. TSMR2020CSCU

Description: MSLC MB Rgls 200A 20/40 S UGOH HB Xcel

UPC No 783164199406

Products > Load Centers > Residential Load Centers > Meter Socket

200A Meter Socket Load Center 20 Circuit Ringless Surface Mount

Descriptors

Category	Meter Socket
GO Schedule	RB

Specifications

Input/Output Voltage	120/240V ac
Type	Breaker
Interrupting Capacity Rating	22
Amperage	200 A
Device Type	Meter Socket
Enclosure	Surface Type 3R
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	2
1" Space	20
1/2" Space	24, 6, 12, 16, 20
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Outline Drawing for Part # TSMR2020CSCU	TSMR2020CSCU	Drawings-Outline and Dimensional
Main Breaker THQMV - Ringless - 200A 22K- 20/40 Circuits - N3R Encl - Surface Front - UG/OH Incoming Feed-Horn Byp - XCEL Listed Outdoor Load Center	10103091-SH69	Drawings-Outline and Dimensional
1 page outline drawing in pdf format.		

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.