

Lighting | Bulbs and Lamps | Miniature Bulbs and Lamps

| 6.0 Watts Incandescent Lamp, S6, Double Contact Bayonet (BA15d), 45 Lumens, 2700K Bulb Color Temp.

[View Product Family](#)

Email Print

GE LIGHTING

6.0 Watts Incandescent Lamp, S6, Double Contact Bayonet (BA15d), 45 Lumens, 2700K Bulb Color Temp.

Item # **4V754** Mfr. Model # **6S6DC-120V** Catalog Page # **N/A** UNSPSC # **39101612**



List Price
Price
\$5.35 / each

Get This Price
\$4.61

Auto-Reorder Every 1 Month

Deliver one time only

1 **ADD TO CART**

[+ Add to List](#)

Confirm ZIP Code to determine availability.

97005
SAVE

☆☆☆☆☆ [Be the first to write a review](#)

Shipping Weight **0.02 lbs.**

How can we improve our [Product Images?](#)

Compare

Country of Origin **USA** | *Country of Origin is subject to change.*

Note: Product availability is real-time updated and adjusted continuously. The product will be reserved for you when you complete your order. [More](#)

TECHNICAL SPECS

Item	Incandescent Lamp
Overall Bulb Shape	S
Bulb Shape	S6
Watts	6.0
Bulb Base Type	Double Contact Bayonet (BA15d)

Shatter-Resistant	No
Bulb Designation	6S6/DC
Light Appearance	2700 to 2999K, Soft White
Bulb Type	Miniature
Dimmable	Yes

Lumens	45
--------	-----------

Bulb Finish	Clear
-------------	--------------

Bulb Color Temp.	2700K
------------------	--------------

Light Technology	Incandescent
------------------	---------------------

Voltage	120
---------	------------

Bulb Primary Application	Appliances
--------------------------	-------------------

Max. Overall Bulb Length	1-13/16"
--------------------------	-----------------

Light Bulb Dia.	3/4"
-----------------	-------------

Average Bulb Life	1500 hr.
-------------------	-----------------

Standards	Meets 2012 Lighting Legislation Energy
-----------	---

How can we improve our [Technical Specifications?](#)


COMPLIANCE AND RESTRICTIONS

Meets U.S. Federal minimum energy-efficiency standards (Circle E).

ALTERNATE PRODUCTS

Alternate Products may not be identical in style or function to original selection. Please compare below for more information.

Compare



ITEM # **4RZW5**

6.0 Watts Incandes

LUMAPRO

List Price
\$1.48 / each

[Get This Price](#)
\$1.24






ALTERNATE SEARCH TERMS

- Incandescent Lamps (1646)
- Incandescent Bulbs (1612)
- Incandescent Light Bulbs (1605)
- Clear Incandescent Lamps (575)
- Appliance Bulbs (78)
- Appliance Lamps (78)
- Appliance Light Bulbs (78)
- Appliance Incandescent Lamps (46)

RELATED PRODUCTS






1 of [PREV](#) | [NEXT](#)



 <p>ITEM # 5KH67 Lamp Recycling Kit RECYCLEPAK List Price \$109.85 / each Get This Price \$89.56</p>	 <p>ITEM # 4LZ57 Lighting Dimmer, S LUTRON List Price \$37.10 / each</p>	 <p>ITEM # 4LZ39 Lighting Dimmer, R LUTRON List Price \$46.55 / each</p>	 <p>ITEM # 4LX84 Lighting Dimmer, T LUTRON List Price \$22.39 / each</p>	 <p>ITEM # 4X603 Lighting Dimmer, T LUTRON List Price \$10.32 / each</p>
---	--	--	--	--

CUSTOMERS ALSO PURCHASED

1 of [PREV](#) | [NEXT](#)

 <p>Black Flame Retard ITEM # 2A225 SCOTCH List Price \$8.22 / each Get This Price \$6.58</p> <p style="text-align: center;">1 ADD TO CART 1</p>	 <p>Socket Bit, 1/2 in. D ITEM # 1AP05 PROTO List Price \$20.51 / each Get This Price \$16.41</p> <p style="text-align: center;">1 ADD TO CART 1</p>	 <p>250VAC Nonreject ITEM # 6F450 EATON BUSSMANN List Price \$30.15 / each</p> <p style="text-align: center;">1 ADD TO CART 1</p>	 <p>DEET-Free Outdoor ITEM # 54FY57 NATULAR List Price \$19.93 / pkg. of 12</p> <p style="text-align: center;">1 ADD TO CART 1</p>	 <p>Cleaver for Single ITEM # 22EN60 GREENLEE COMMUNIC List Price \$1,302.00 / each</p> <p style="text-align: center;">1 ADD TO CART 1</p>
---	---	--	--	---

CUSTOMER REVIEWS

REVIEWS

WRITE REVIEWS



This Product has no Reviews. Be the first to [Write a Review](#).

Product Reviews Disclaimer:

Grainger is neither responsible for, nor does it endorse, the content of any product review or statement posted. Any statements posted constitute the statements of the poster and are not the statements of Grainger. The statements posted by Grainger employees with the Grainger employee badge represent the views of such employees and are not the statements of Grainger. Grainger makes no representations as to the appropriateness, accuracy, completeness, correctness, currentness, suitability, or validity of any product review or statements posted, including those posted by employees with the Grainger employee badge, and is not liable for any losses, injuries or damages which may result from any such product review or statements. Use of any linked web site provided in a product review or post is at the user's own risk.