



Catalog No. CR305H002

Description:

UPC No

Products > Contactors > NEMA Contactors > 300 Line Full Voltage Magnetic Contactors

NEMA Rated Full Voltage Contactors. Magnetic Contactors. Single-phase, One- and Two-Pole. Nonreversing, Open, NEMA Type 1, 3R, 12, 4/4X. NEMA Sizes 00-9. 600 Volts Maximum 50/60 Hertz. CR305, Single-Phase, 2-Pole Magnetic Contactors NEMA sizes 00-6. Motor full-load current should not exceed continuous ampere rating of contactor.

Descriptors

Category	300 Line Full Voltage Magnetic Contactors
GO Schedule	10G

Specifications

Continuous Current	10 A
Enclosure Type	Open Type
Horsepower	0.33 hp