




SRC Universal Ground Rod Clamp

- Bronze alloy or stainless steel hardware both UL listed and approved for direct burial in earth and concrete.
- Performs the functions of economy, standard duty, heavy duty, and extra heavy duty.
- Able to withstand torque in excess of 350 in/lb.
- RUS listed.



One Clamp Fits 1/2, 5/8 and 3/4 Rod Diameters.

Catalog Number	Rod Size	Conductor Range	Sub & Master Pack	Wt. Per 100	NAED UPC No. 632591-
SRC	1/2"	1/0 Str. - 10 Sol.	100	16	613286
SRC	5/8"	1/0 Str. - 10 Sol.	100	16	613286
SRC	3/4"	1/0 Str. - 10 Sol.	100	16	613286

Notes: Listed for galvanized and copper ground rods
UL Listed for US and Canada

This clamp accommodates all 1/2 and 5/8-inch rod diameters, and 3/4-inch copper-coated rods only. Will not fit 3/4-inch full-size galvanized, stainless steel or solid copper rods.

Ground Rod Clamps (Hex-Head)

- Bronze alloy or stainless steel hardware both UL listed approved for direct burial in earth and concrete.
- Cast copper alloy body with hex head bolt provides simple trouble-free connection at low cost.



Catalog Number	Rod Size	Conductor Range	Sub & Master Pack	Wt. Per 100	NAED UPC No. 632591-
G-3	3/8"	4 Str. - 10 Sol.	100 / 800	6	70706-0
G-4*(Use G-5)	1/2"	2 Str. - 10 Sol.	100 / 800	9	70707-7
G-5*§	5/8-1/2"	2 Str. - 10 Sol.	50 / 400	10	70708-4
G-6*†	3/4"	2 Str. - 10 Sol.	50 / 400	11	70709-1

Notes: *-These items UL and CSA Listed in US and Canada for direct burial in earth and concrete.

†-The G-6 fits all 3/4-inch diameter rods regardless of actual or nominal diameter.

§- This item UL Listed for use on 1/2" and 5/8" copper-coated and galvanized rods, and #4 (1/2") rebar, buried in earth or concrete. Also RUS Listed.

Ground Rod Clamps (Hex-Head Tin-Plated)

- Bronze alloy or stainless steel hardware approved for direct burial in earth and concrete.
- Cast copper alloy body with hex head bolt provides simple trouble-free connection at low cost on galvanized ground rods.



Catalog Number	Rod Size	Conductor Range	Sub & Master Pack	Wt. Per 100	NAED UPC No. 632591-
G3P	3/8"	4 Str. - 10 Sol.	100 / 800	6	61135-0
G4P*	1/2"	2 Str. - 10 Sol.	100 / 800	9	61219-7
G5P*	5/8-1/2"	2 Str. - 10 Sol.	50 / 400	10	61220-3
G6P	3/4"	2 Str. - 10 Sol.	50 / 400	11	61221-0

Notes: * RUS Listed and marked per RUS specification and traceability.

Heavy-Duty Ground Rod Clamps (Hex-Head)

- Bronze alloy or stainless steel hardware both UL listed approved for direct burial in earth and concrete.
- Ground connection is secured by long bearing surface of clamp on ground wire.
- High-strength corrosion-resistant copper alloy. All Heavy Duty clamps UL Listed for direct burial in earth and concrete.



Catalog Number	Rod Size	Conductor Range	Sub & Master Pack	Wt. Per 100	NAED UPC No. 632591-
JAB12H	1/2"	2 Str. - 10 Sol.	100 / 800	12	70715-2
JAB58H	5/8"	1/0 Str. - 8 Sol.	50 / 400	13	70716-9
JAB58HH*	5/8"	1/0 Str. - 8 Sol.	50 / 400	14	61311-8
JAB34H	3/4"	1/0 Str. - 8 Sol.	25 / 250	15	70717-6
JAB34HH	3/4"	3/0 Str. - 8 Sol.	25 / 200	17	61495-5
JAB1H	1"	4/0 Str. - 8 Sol.	50 / 400	25	70718-3

Notes: *-HH represents "Heavy duty hex head design screw 1/2" - 13 threads

-These items UL and CSA Listed except for JAB58HH and JAB34HH

JAB58H Listed for US and Canada - 7/16 -14 threads