

GUARDIAN® SERIES 25-60 kW AUTOMATIC STANDBY GENERATORS



Robust backup power protection for large homes and small businesses



Smart, User Friendly Controls

Control generator diagnostics and get information at a glance with Generac's user-friendly Nexus™ Controller—the most comprehensive available.



Weather-Resistant Enclosures

Our galvanneal steel enclosures feature the RhinoCoat™ finish system, which evenly joins paint particles to every part of the metal surface for consistent coverage and exceptional protection.



Rugged Commercial Engines

These commercial engines are built to withstand the rigors of generator use, and pack more power into a smaller footprint than many competitive engines.



Remote Monitoring From the Comfort of Home

Generac's wireless remote monitors (sold separately) allow you to observe generator status, set operation parameters and more—all without leaving the comfort of your home.

Stand Up to Unpredictable Power Outages

Whether it's due to severe weather or simply an equipment malfunction, Generac's Guardian® Series can back up all of your home's circuits during a power outage. Or protect your bottom line by keeping your business up and running. Connected to the existing LP or natural gas fuel supply, it kicks in within seconds of determining power loss—automatically—and runs for as long as necessary until utility power returns. With Generac's Guardian Series, life won't miss a beat.

25-60 KILOWATTS

Ideal for larger homes requiring complete whole-house coverage, and small to medium sized businesses.



- Generac's automotive-style liquid cooled engine packs more power into a smaller footprint than many competitive engines
- Easily connects to existing LP or natural gas fuel supply; quickly convert in the field for up to 45kW
- Quiet-Test™ weekly self-test mode - runs at a lower RPM and is quieter than other brands, consumes less fuel, and produces fewer emissions
- Galvanneal steel enclosures feature RhinoCoat™ finish for superior weather protection

Rated Power (liquid propane/natural gas)	25/25 kW	30/30 kW	45/45 kW	45/45 kW	60/60 kW	60/60 kW
Generator Model#	QT02515ANSX	QT03015ANSX	QT04524ANSX	QT04524ANSC	QT06024ANSX	QT06024AVSX
Voltage (Single Phase)	240V					
Amps @ 240V LPG	104	125	188	188	N/A	250
Amps @ 240V NG	104	125	188	188	250	N/A
Engine/Alternator RPM	3600/3600					
Engine	In-line 4-Cylinder					
Fuel Consumption @ full load LPG cu. ft/hr (gal.hr)	172 (4.7)	197 (5.4)	290 (8)	290 (8)	N/A	327 (9)
Fuel Consumption @ full load NG cu. ft/hr (gal.hr)	430	492	730	730	862	N/A
Quiet-Test Mode	Yes					
db(A) at exercise	59	59	61	61	65	65
db(A) at normal operating load	72	73	73	73	72	72
Automatic Transfer Switch	Not Included					
Enclosure	Steel					
Enclosure Color	Bisque					
Warranty	2 Year Limited					
Dimensions (L" x W" x H")	62.2 x 29 x 33.5		77 x 33.5 x 45			
Weight (lbs.)	875	935	1414		1441	
SCAQMD Model	•	•	n/a	•	n/a	n/a

Nationwide Dealer Service Network

Generac's commitment to service includes scheduled maintenance programs, warranty assistance and emergency service to ensure that Generac customers are never left powerless. The largest nationwide dealer network has factory trained technicians on staff and maintains large inventories of Generac parts, components and accessories. Find a dealer near you at generac.com.

GENERAC

Generac Power Systems, Inc.
S45 W29290 Hwy. 59
Waukesha, WI 53189



Bulletin 0194060SBY Printed in USA 2.2012
©2012 Generac Power Systems, Inc. All rights reserved.
Specifications are subject to change without notice

generac.com 1-888-GENERAC (1-888-436-3722)