



Offshore and  
Marine Shipboard  
Cables

# IEEE 1580 Type P MOR™ Polyrad® XT-125



**Flexible Multi Conductor Power  
Armored & Sheathed**  
600V/1000V



Catalog Number (T-75126)	# of Cores	Cond. Size (AWG)	Nominal Cable Diameter		Net Weight		Ampacities* 45°C Ambient-Single Banked			
			Inches	mm	lbs/1000 ft.	kg/km	95°C	100°C	110°C	125°C
279250	4	8	0.919	23.35	684	1018	40	42	45	50
279270	4	6	1.013	25.73	890	1325	54	56	60	73
357090	4	5	1.210	30.74	1223	1820	62	66	70	96
291730	4	4	1.259	31.97	1358	2021	70	74	79	101
357100	4	3	1.319	33.50	1547	2302	82	86	93	118
302610	4	2	1.403	35.64	1711	2546	93	98	105	129
302620	4	1	1.663	42.24	2543	3784	110	114	122	162
355660	4	1/0	1.781	45.24	2910	4331	126	131	141	183
302630	4	2/0	1.963	49.86	3484	5185	144	150	161	203
302640	4	3/0	2.202	55.94	4403	6553	167	174	186	250
296180	4	4/0	2.360	59.95	5220	7768	194	202	216	283
357110	4	262	2.457	62.40	5816	8655	226	235	248	316
357120	4	313	2.626	66.69	6697	9966	247	257	276	354
357130	4	373	2.842	72.19	8040	11965	289	300	325	394

357140	5	8	0.986	25.05	800	1191	40	42	45	50
357150	5	6	1.132	28.75	1151	1713	54	56	60	73
357160	5	5	1.306	33.17	1402	2086	62	66	70	96
357170	5	4	1.360	34.54	1584	2357	70	74	79	101
357180	5	3	1.428	36.26	1806	2688	82	86	93	118
357190	5	2	1.522	38.66	2074	3087	93	98	105	129
357200	5	1	1.806	45.87	3132	4661	110	114	122	162
357210	5	1/0	1.998	50.76	3645	5424	126	131	141	183
357220	5	2/0	2.101	53.37	4244	6316	144	150	161	203
357230	5	3/0	2.396	60.86	5519	8213	167	174	186	250
357240	5	4/0	2.539	64.49	6228	9269	194	202	216	283
357250	5	262	2.758	70.05	6415	9546	226	235	248	316
357260	5	313	2.926	74.32	7399	11,010	247	257	276	354
357130	5	373	2.842	72.19	8040	11965	289	300	325	394

\* Reference Ampacity section