

IEEE 1580 Type P MOR™ Polyrad® XT-125



Flexible Multi Conductor Control
Armored & Sheathed, 14 AWG, 12 AWG & 10 AWG
600V/1000V



Catalog Number (T-75126)	# of Cores	Cond. Size (AWG)	Nominal Cable Diameter		Net Weight		Ampacities* 45°C Ambient-Single Banked			
			Inches	mm	lbs/1000 ft.	kg/km	95°C	100°C	110°C	125°C
326120	2	14	0.575	14.60	235	350	30	31	33	33
279320	3	14	0.595	15.11	265	394	24	25	27	28
279310	4	14	0.635	16.13	306	455	19	20	22	22
281180	5	14	0.670	17.02	343	510	19	20	22	22
302600	6	14	0.710	18.03	383	570	19	20	22	22
281170	7	14	0.710	18.03	403	600	17	18	19	20
356760	8	14	0.755	19.18	448	667	17	18	19	20
279170	10	14	0.880	22.35	574	854	12	13	14	14
352480	12	14	0.910	23.11	635	945	12	13	14	14
315770	14	14	0.940	23.88	689	1025	12	13	14	14
356770	16	14	0.960	24.38	779	1159	12	13	14	14
279180	20	14	1.045	26.54	877	1305	12	13	14	14
315820	24	14	1.195	30.35	1074	1558	10	11	12	13
356780	30	14	1.260	32.00	1244	1851	10	11	12	13
279190	37	14	1.325	33.65	1419	2112	9	10	11	11
356790	44	14	1.475	37.46	1676	2494	8	9	10	10
356800	60	14	1.670	42.42	2221	3305	8	9	10	10
356810	91	14	2.020	51.31	3231	4808	7	8	9	8

281160	2	12	0.615	15.62	274	408	38	40	43	44
279200	3	12	0.640	16.26	316	470	30	31	33	37
279210	4	12	0.675	17.14	362	539	24	25	26	30
356820	5	12	0.730	18.54	422	628	24	25	26	30
356830	6	12	0.765	19.43	466	694	24	25	26	30
355760	7	12	0.765	19.43	495	737	21	22	23	26
356840	8	12	0.815	20.70	552	821	21	22	23	26
287710	10	12	0.955	24.26	709	1055	15	16	17	19
356850	16	12	1.005	26.80	1163	1731	15	16	17	19
281210	20	12	1.205	30.61	1185	1764	15	16	17	19
356860	24	12	1.270	32.27	1431	2129	13	14	15	17
356870	30	12	1.330	33.78	1632	2429	13	14	15	17
287730	37	12	1.460	37.08	1853	2758	12	13	14	15
356880	44	12	1.575	40.01	2066	3074	10	11	12	13
356890	60	12	1.850	46.99	2929	4359	10	11	12	13
356900	91	12	2.155	54.74	3562	5301	8	9	10	11

* Reference Ampacity section