

Industrial Control Transformers

Conductor	Temp Rise (Celsius)	Electro-static Shield	Primary/Secondary	Part Number	Wiring Diagram	Taps	Dimensions (inches)			Weight (lbs)
							H	W	D	
CU	55°	N	240x480V - 120V 230x460V - 115V 220x440V - 110V	FA050JK	IC1	N	2.562	3	3	2.6
				FA075JK			2.562	3	3.5	3.5
				FA100JK			2.875	3.375	3.375	4.2
				FA150JK			3.187	3.75	4	6.7
				FA200JK			3.812	4.5	4	8.5
				FA250JK			3.812	4.5	4.375	10
				FA300JK			3.812	4.5	4.75	11.3
				FA350JK			3.812	4.5	5.25	13.6
				FA500JK			4.75	5.25	5.5	19.2
				FA750JK			4.75	5.25	7	28.1
			240x480V - 24V	FB050JK	IC2	N	2.562	3	3	2.7
				FB075JK			2.562	3	3.5	3.5
				FB100JK			2.875	3.375	3.375	4.2
				FB150JK			3.187	3.75	4	6.7
				FB200JK			3.812	4.5	4	8.5
				FB250JK			3.812	4.5	4.375	10.1
				FB300JK			3.812	4.5	4.75	11.4
				FB350JK			3.812	4.5	5.25	13.4
			FB500JK	4.75	5.25	5.625	17.5			
			120x240V - 24V	FC050JK	IC3	N	2.562	3	3	2.6
				FC075JK			2.562	3	3.5	3.6
				FC100JK			2.875	3.375	3.375	4.4
				FC150JK			3.187	3.75	4	6.7
				FC200JK			3.812	4.5	4	8.3
				FC250JK			3.812	4.5	4.375	10.1
				FC300JK			3.812	4.5	4.75	11.2
				FC350JK			3.812	4.5	5.25	13.2
			FC500JK	4.75	5.25	5.625	17.5			
			208/277V - 120V	FF050XK	IC4	N	2.562	3	3	2.9
				FF075XK			2.562	3	3.5	3.8
				FF100XK			2.875	3.375	3.375	4.5
				FF150XK			3.187	3.75	4	6.9
				FF200XK			3.812	4.5	4	8.7
				FF250XK			3.812	4.5	4.375	10.2
				FF300XK			3.812	4.5	4.75	11.4
				FF350XK			3.812	4.5	5.25	13.7
				FF500XK			4.75	5.25	5.375	17.2
			FF750XK	4.75	5.25	7	25.7			
			200/220/440V - 23/110V 208/230/460V - 24/115V 240/480V - 25/120V	FJ050XK	IC5	N	2.562	3	3.25	3.4
				FJ075XK			2.875	3.375	3.5	4.8
				FJ100XK			3.187	3.75	3.625	5.9
				FJ150XK			3.187	3.75	4.375	7.9
				FJ200XK			3.812	4.5	4.5	10.6
				FJ250XK			3.812	4.5	5.25	13.9
				FJ300XK			4.75	5.25	5.125	15.5
				FJ350XK			4.75	5.25	5.375	16.8
			FJ500XK	4.75	5.25	6.875	23.4			
			240x480 - 120x240	FK050JJ	IC6	N	2.562	3	3	2.6
				FK075JJ			2.562	3	3.5	3.5
				FK100JJ			2.875	3.375	3.375	4.2
FK150JJ	3.187	3.75		4			6.7			
FK200JJ	3.812	4.5		4			8.5			
FK250JJ	3.812	4.5		4.375			10			
FK300JJ	3.812	4.5		4.875			11.8			
FK350JJ	3.812	4.5		5.25			13.6			
FK500JJ	4.75	5.25		5.25			17.5			
FK750JJ	4.75	5.25	7	26.4						