



Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.*	Description	Class, Filament	LCL (In.)	MOL (In.)	Rated Avg. Life, Hrs. (93)	Approx. MBCP*	Lumens
DuraMax® Long Life Reflectors														
30	R-20	Med.	16753-6	▲ (87)	30R20/LL 12/I	120	12	Frost Long Life Reflector	C, CC-6	3 1/8	3 1/8	2500	350	205
45	BR-30	Med.	16751-0	▲ (87)	45BR30/FL55/LL 12/I	120	12	Long Life Reflector Flood	C, CC-6	5 3/8	5 3/8	2500		340
50	BR-19	Med.	16750-2	▲\$ □ (87)	50BR19/25/SP/LL 12/I	120	12	Long Life Spotline Reflector	C, CC-11	4 1/8	4 1/8	2500	700	385
	R-20	Med.	16755-1	▲ (87)	50R20/LL 12/I	120	12	Frost Long Life Reflector	C, CC-6	3 1/8	3 1/8	2500	600	385
65	BR-30	Med.	16768-4	▲ (87)	65BR30/FL55/LL 12/I	120	12	Long Life Reflector Flood	C, CC-6	5 3/8	5 3/8	2500	510	595
			16769-2	▲ (87)	65BR30/SP20/LL 12/I	120	12	Long Life Reflector Spot	C, CC-6	5 3/8	5 3/8	2500	530	610
	BR-40	Med.	16741-1	▲ (87)	65BR/FL60/LL 8/I	120	8	Long Life Reflector Flood	C, CC-6	6 1/2	6 1/2	2500	500	630
75	R-20	Med.	16763-5	▲ (87)	75R20/LL 12/I	120	12	Frost Long Life Reflector	C, CC-6	3 1/8	3 1/8	2500	1250	570
85	BR-30	Med.	16766-8	▲ (87)	85BR30/FL55/LL 6/I	120	6	Long Life Reflector Flood	C, CC-6	5 3/8	5 3/8	2500	700	855
			16767-6	▲ (87)	85BR30/SP20/LL 6/I	120	6	Long Life Reflector Spot	C, CC-6	5 3/8	5 3/8	2500	3100	865
	BR-40	Med.	16785-8	▲ (87)	85BR/FL60/LL 8/I	120	8	Long Life Reflector Flood	C, CC-6	6 1/2	6 1/2	2500	700	900
			16788-2	▲ (87)	85BR/SP20/LL 8/I	120	8	Long Life Reflector Spot	C, CC-6	6 1/2	6 1/2	2500	3100	900
100	R-20	Med.	16701-5	▲ (87)	100R20/LL 12/I	120	12	Frost Long Life Reflector	C, CC-6	3 1/8	3 1/8	2500		935
120	BR-40	Med.	16779-1	▲ (87)	120BR/FL60/LL 8/I	120	8	Long Life Reflector Flood	C, CC-6	6 1/2	6 1/2	2500	1000	1285
			16781-7	▲ (87)	120BR/SP20/LL 8/I	120	8	Long Life Reflector Spot	C, CC-6	6 1/2	6 1/2	2500	4600	1225

DuraMax® Long Life Sparkling Clear

40	A-19	Med.	16797-2	▲	40A/CL/LL 12/2	120	24	Clear Long Life	C, CC-6	4 3/8	4 3/8	1500		505
60	A-19	Med.	16794-0	▲	60A/CL/LL 12/2	120	24	Clear Long Life	C, CC-6	4 3/8	4 3/8	1500		900
75	A-19	Med.	16801-3	▲	75A/CL/LL 12/2	120	24	Clear Long Life	C, CC-6	4 3/8	4 3/8	1500		1080
100	A-19	Med.	16795-6	▲	100A/CL/LL 12/2	120	24	Clear Long Life	C, CC-6	4 3/8	4 3/8	1500		1470
150	A-21	Med.	16799-8	▲	150A/CL/LL 12/1	120	12	Clear Long Life	C, CC-8	5 3/8	5 3/8	2000		2570
200	A-23	Med.	16798-0	▲	200A/CL/LL 6/1	120	6	Clear Long Life	C, CC-8	6 3/8	6 3/8	1500		3665

DuraMax® Long Life Fan Lights

40	A-15	Med.	16934-2	▲	BC40A15/FAN/CL/LL 6/2	120	12	Clear Long Life Fan	C, C-9	3 1/2	3 1/2	2000		395
			16935-9	▲	BC40A15/FAN/W/LL 6/2	120	12	White Long Life Fan	C, C-9	3 1/2	3 1/2	2000		365
60	A-15	Med.	16945-8	▲	BC60A15/FAN/W/LL 6/2	120	12	White Long Life Fan	C, C-9	3 1/2	3 1/2	2000		570
			16946-6	▲	BC60A15/FAN/CL/LL 6/2	120	12	Clear Long Life Fan	C, C-9	3 1/2	3 1/2	2000		630

DuraMax® Long Life Decoratives

3	CA-10	Med.	16697-4	▲ (12)	BC3CA10/CL/LL 6/1	120	6	Clear Long Life Flicker Flame	B, CC-2V	3 3/8	3 3/8	2000		
		Cand.	16698-2	▲ (12)	BC3CA10C/CL/LL 6/1	120	6	Clear Long Life Flicker Flame	B, CC-2V	4 1/8	4 1/8	2000		
15	BA-9	Cand.	16811-2	▲ (12)	BC15BA9C/CL/LL 6/2	120	12	Clear Long Life Bent Tip	B, CC-2V C-7A	4 3/8	4 3/8	2000		110
			16696-6	▲ (12)	BC15BA9C/CL/LL 6/4	120	24	Clear Long Life Bent Tip	B, CC-2V C-7A	3 3/8	3 3/8	2000		110
	F-10	Cand.	16830-2	▲ (12)	BC15F10C/CL/LL 6/2	120	12	Clear Long Life Flame	B, C-7A	3 1/8	3 1/8	2000		95
			16831-0	▲ (12)	BC15F10C/A/LL 6/2	120	12	Amber Long Life Flame	B, C-7A	3 1/8	3 1/8	2000		85
25	BA-9	Cand.	16719-7	▲ (12)	BC25BA9C/CL/LL 6/4	120	24	Clear Long Life Bent Tip	C, CC-2V C-7A	4 3/8	4 3/8	2000		150
			16806-2	▲ (12)	BC25BA9C/CL/LL 6/2	120	12	Clear Long Life Bent Tip	C, CC-2V C-7A	4 3/8	4 3/8	2000		150
			16810-4	▲ (12)	BC25BA9C/F/LL 6/2	120	12	Frost Long Life Bent Tip	C, CC-2V C-7A	4 3/8	4 3/8	2000		145

For the most current product information, go to www.nam.lighting.philips.com/us/ecatalog/

Incandescent symbols and footnotes located on page 50

