



Energy Advantage T8

F32T8/ADV841/EW/ALTO 28W 30PK

Philips Energy Advantage T8 lamps offer high energy savings without sacrificing performance.

Product data

• General Information

Cap-Base	Medium Bi-Pin [Medium Bi-Pin]
Bulb Shape	T8 [T8 (T8)]
Life 12-Hr Program-start [Hrs]	44000 h
Life 12-Hr Instant Start [Hrs]	38000 h
Life 3-Hr Program Start [Hrs]	38000 h
Life 3-Hr Instant Start [Hrs]	32000 h
Features	ALTO® (ALTO)
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

• Light Technical

Color Code	Advantage 841 [CCT of 4100K (842)]
Initial lumen (Nom)	2725 lm
Color Designation	Advantage 841
Design Mean Lumens	2645 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	82

• Operating and Electrical

Power (Rated) (Nom)	28 W
---------------------	------

• Mechanical and Housing

Cap-Base Information	Green Base
Nominal Length (Inch)	48

• Approval and Application

Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	27 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

• Product Data

Order product name	F32T8/ADV841/EW/ALTO 28W 30PK
EAN/UPC - Product	046677281038
Order code	281030
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927852284204
Net Weight (Piece)	0.001 kg

PHILIPS

Warnings and Safety


- It's strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Dimensional drawing


F32T8 28W/842 EW ALTO ES

Product

F32T8/ADV841/EW/ALTO 28W 30PK



G13, T8



© 2015 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, November 29
data subject to change