

e-Catalog Search



F32T8/SPX50/ECO2

68853

91

lumens/watt

F32T8/SPX50/ECO2

[Specifications](#)

GENERAL CHARACTERISTICS

| | |
|---------------------------------|---------------------------------|
| Base Description | Medium Bi-Pin |
| Base Type | Pin/Plug-In |
| Mercury Content | 2.95 mg |
| Mercury-Picogram per mean lm hr | 35.7 |
| Rated Life Instant Start-Hrs | 21000 h @ 3 h 30000 h @ 12 h |
| Rated Life Rapid Start - Hrs | 30000 h @ 3 h 36000 h @ 12 h |
| Starting Temp (MIN) C-degrees | 10 °C |
| Bulb Material | Sodalime glass |
| Rated Life Hours-nominal | 30000 h |
| Primary Application | Full Wattage |
| Product Technology | Linear Fluorescent |
| Base | G13 |
| Bulb Shape | T8 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|------|
| Rated power (Watts) | 32 W |
|---------------------|------|

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Mean Lumens nominal | 2755 lm |
| Nominal Initial Lumen per Watt | 91 |
| Initial Lumens-nominal | 2900 lm |
| Color Rendering Index-CRI | 82 |
| Color Temperature | 5000 K |

DIMENSIONS

| | |
|----------------|---------|
| Diameter | 1.0 in |
| Nominal Length | 48.0 in |

PACKAGING INFORMATION

| | |
|-----------------------------|----------------|
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | 36 |
| Ean UPC | 043168688536 |
| Standard Package GTIN | 10043168688533 |
| Length | 48.81 in |
| Width | 7.88 in |
| Height | 7.31 in |
| Volume | 1.62708 cuft |
| Gross Weight | 20.0 lb |
| Pack Level Description | Case |
| Sales Unit | Case |
| UCC | 043168688536 |