



GE  
Lighting

### 73096 - GE Ecolux® Starcoat® T8 - Office

F32T8SXLSPX50ECO

Super long life

#### GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	20
Rated Life Instant Start-Hrs	31000 h @ 3 h 40000 h @ 12 h
Rated Life Rapid Start - Hrs	55000 h @ 3 h 60000 h @ 12 h
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	55000 h
Primary Application	Office
	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2630 lm
Nominal Initial Lumen per Watt	88
Initial Lumens-nominal	2800 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

#### PRODUCT INFORMATION

Product Code	73096
Description	F32T8SXLSPX50ECO
Alternative Unit Of Measure	CASE

#### DIMENSIONS

Diameter	1.0 in
Nominal Length	48.0 in

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	32 W
---------------------	------

