

# GLOBEX™

Catalog #:	PLC-26W/27/4P
Brand:	Globex / E Team
Part #:	653329
Volts AC	120
Wattage:	26
Color Temperature:	2700 (Warm)
Length:	6 1/2 in
Lumens:	1430
UPC:	74941453329
Base Type:	G24Q-3, 4-Pin
CRI:	85
Life Hours:	8000



## Advanced High-Efficiency Features:

- Emits light comparable to an 130-Watt bulb at a fraction of the energy consumption.
- 90% power factor.
- Harmonic Distortion <25%
- Uses 80% less electricity than standard household light bulbs.
- Lasts up to 10 time longer than standard household light bulbs (based on a 3-hr start per operation).
- Soft warm white lighting.
- Turns on instantly and operates silently.
- Initial Output: 1430 Lumens
- Designed to meet UL Standards.

*Use with Electronic Ballast's*

*Do not use light bulb with dimmer.*

## For best operation:

- Never use the following fixtures: Emergency Light Fixtures, Direct Current Fixtures, Dimming Circuit Fixtures, Closed Fixtures.
- Never install where water may drop on the lamp.
- Never install where the ambient temperature may rise above 40°C.
- Never use on a source voltage that may fluctuate over  $\pm 10\%$  of the lamp's rated voltage.
- Unsuitable for applications where the lamp must be turned on and off frequently.